


How to measure



© 05/2019



MAXI STANDARD, BLACK OUT, MAXI LUX

Installation between glass holders (in the light aperture)

1. How to define the width – measure precisely the width of the glass in the upper, medium and bottom part of the window with accuracy to mm, take the smallest of the three values and subtract 0.2 cm.
2. How to define the height – measure precisely the height of the glass in the left and right part of the window with accuracy to mm, take the smaller of the two values and subtract 0.5 cm (when the blinds are to be made with side guiding, subtract 1.0 cm).
3. Control of the blinds – you define whether to be left or right (depending how it is viewed from the room). It is recommended for the control to be on the side of the hinges.